

SONICA[®] 4200 S3

Product name	Code
SONICA 4200 M S3 *	090.003.0022
SONICA 4200 MH S3 *	090.003.0023
SONICA 4200 ETH S3 *	090.003.0024
SONICA 4200 EP S3 *	090.003.0025
Ultrasonic Cleaner 14 Litres	

Accessories

Stainless steel wire basket Internal dim. 285x260x85mm	090.004.0007
Stainless steel lid 4200/4300	090.004.0023
Stainless steel auxiliary tank SONICA 4200 Indicative dim. 330x300x150mm	090.004.0045
Stainless steel beaker holder for two glass or plastic beaker	090.004.0036
Plastic beaker 250 ml	090.004.0032
Glass beaker 400 ml	090.004.0033

Further accessories on request



* Stainless steel tank made in AISI 304 thickness 08/10 with round tank corners for a better removing of dirt residuals after cleaning process. The tank is conical and realized with a press machine

General Characteristics

Ultrasonic Cleaning is a safe and efficient modern procedure, which ensures perfect cleaning within the shortest time possible. It has many advantages over ordinary cleaning methods. Ultrasonics can remove even the most tenacious deposits from parts which would be difficult to reach by hand, it also reduces the risk of injury or infection which may occur during manual cleaning.

Notes for use as "Medical Devices"

Denomination: Ultrasonic Cleaning Device UMDNS-nomenclature (ECRI) 14-263

Field of application: Cleaning and disinfection of surgical and dental instruments

Classification (Medical Devices Directive 93/42/EEC, appendix IX): Class I, Non Active MD, Non Invasive MD, Non Implantable MD

"Medical Device" registration and classification

Registration Number: 103291/R SOLTEC Srl **CND Classification:** Z12011302 Ultrasonic Cleaning Device

SOLTEC S.r.l.

Uffici Commerciali e Sede Legale: Via G. Röntgen 16 - 20136 Milano
Tel. +39 02 58 308 378 - Fax +39 02 58 308 595 - www.soltec.it - info@soltec.it
Produzione e Magazzino: Via G. Castelbarco, 17 - 20136 Milano - Tel. +39 02 58 324 131

Cod. fisc. e P.IVA: IT11127210158
N. Mecc.: MI 221750 - C.C.I.A.A. Milano N. 1441548
Iscr. Trib. Mi Reg. Soc. N. 343391/8444/41
Cap. Soc. Euro 110.500 i.v. - Iscr. Registro AEE Nr. IT08020000000435



SONICA[®] 4200 S3

Technical specification subject to change

Technical Data

Main line voltage	230/240V~50/60Hz
Main input power/consumption	300 W
Main input power with heating	800 W
Peak HF Ultrasound Power	600 W
US frequency	39 kHz \pm 1 kHz with SWEEP SYSTEM Technology
Liquid drain	1/2"
Transducers	4 (2 Piezoelectric ceramics each)
Tank capacity [L]	14
Weight [KG]	6,8
Installation category	Class II according to EN 61010-1
Environmental conditions	Temperature Rel. Hum. 80% up to 31°C with linear decrease up to 50% at 40°C
IP grade	IP 22
CE-compliant	2004/108/EC EMC Directive (EN61326) 2006/95/EC LV Directive (EN 61010-1) 93/42/CEE Medical Device Directive Risk Class I according to the rule 12 to the Directive 93/42/EEC Annex IX

Approximately Internal Tank Dimensions


W/D/H (mm)	330 / 300 / 150
Max filling volume tank	14 L

External Appliance Dimensions

W/D/H (mm)	440 / 340 / 425
Max operating tank volume	11,8 L

Constructive Materials

Housing	Stainless steel AISI 304
Tank	Stainless steel AISI 304



Control panel available series



M serie: The simplest version in the SONICA range is equipped with a timer which can be set for 15 minutes. It can also be set to manual operation up to 1 hour of continuous. No heating system
Sweep System generator

MH serie: This version is equipped with a timer which can be set for 15 minutes. It can also be set to manual operation up to 1 hour of continuous. The thermostat for the heater is set at 60°C.
Sweep System generator

ETH serie: Cleaning times and temperature controlled electronically by a microprocessor. Ultrasonic cleaning times 5-10-15 minutes. Double washing times 10-20-30 minutes by pressing twice the minutes key
Sweep System generator

EP serie: The most technologically advanced of the SONICA range: **Sweep System** generator; modern digital display control panel window; degas time setting; cleaning times from 0 to 99 minutes; tank liquid temperature setting up to 70°C; memory for 9 cleaning programmes; jet program function to start quickly and easily cleaning cycle.